


Temp

Climate controlled drug & fluid compartment.
Designed to maintain internal temperature at 70° F*



**Target temperature set to 70 will maintain this setpoint temperature within plus or minus 5 degrees.*

Features Include

- ❄️ **Solid-State Design**
- ❄️ **Automatic Heat/Cool**
- ❄️ **Digital Controller**
- ❄️ **Override Power Switch**
- ❄️ **Fully Insulated Enclosure**
- ❄️ **Sealed Poly-Coat Interior**
- ❄️ **PVC Floor Scuff Plate**
- ❄️ **Self Sealing Door**
- ❄️ **Positive Slam Latch**
- ❄️ **Durable HDP Frame**



Custom Fit Design

Every drug bag and manner in which equipment is stored is different depending on your agency's needs. Templox can be custom made to simply slip into a standard cut-out in an ambulance or response vehicle. Just allow 3" in all dimensions for the enclosure walls and your custom Templox can be fit to your application.






Temp Lux

Specifications, Accessories & Options

THERMAL SPECIFICATIONS

Operating Range	20 to 115°F
Max. Delta-T	40°
Performance	200-220 BTU/Hr.
Control	Fully Digital
Efficiency of Compartment	8.0-12.5 R-Value
Thermal Deviation	5°F

Internal Performance at 40 Degree Change



ELECTRICAL SPECIFICATIONS

Operating Voltage	11-13.8 V DC
Running Current	12 Amps
Standby Current	0.2 Amps
Wattage of Unit	144 Watts
Average Amp Hours at Temp.	3.2 Ahr

ENVIRONMENTAL SPECIFICATIONS


Weight	7.5 LBS*
Size	5.5 X 10 Inches*
Noise	22dB
Enclosure	Nema-12

*Thermoelectric heatpump only. Enclosure not included.

ACCESSORIES & OPTIONS

Heatpump Kit Only


Comes complete with remote mount digital controller, thermoelectric heatpump unit, mounting gasket and override switch. Fully wired, all you provide is the compartment and 12V.



Remember: The controller and heat-pump are just half of the effectiveness of a true Templox unit. The manner, materials and insulation of the enclosure or compartment is key to a successful integration. To minimize the thermal loss, thus reducing the running time of the unit, a well insulated, sealed compartment made from non-conductive materials is required.

Access Control

The optional Videx Touch Access Control give you not only an electronic lock, but an audit trail of who has accessed and attempted to access the enclosure.



PART NUMBERS & ORDERING INFO

Heatpump Kit Only	P020904A
Stand Alone Unit	TLC-2424-P
Self Trimming Ambulance Unit	TLC-AMB-ST
Touch Access 200 Lock	TAC-200

Custom integration into existing vehicle spaces is available. Call for more information.
www.flev.com or 877-327-8526

Authorized Dealer



getinthefastlane.com
The Future of First Response
37241 East Richardson Lane
Purcellville, VA 20132
877-327-8526

www.getinthefastlane.com